

The EPD accessories will provide convenient storage, transport, spare kits and remote visual alarms. Everything you need to maximize the care of your EPD, and minimize the wear and tear.

EPD[®] Accessories

A variety of accessories for your hand-held EPD



EPD Stackable Storage Tray SST-1™

- Strong, stackable plastic tray for 16 EPDs
- Economic, convenient storage, ideal for use in calibration laboratories, and instrument and health physics' workshops
- Helps to maintain EPDs in good condition
- Status of EPDs can be seen at a glance



Wall Rack WR-1™

- Provides convenient, versatile, secure storage for Electronic Personal Dosimeters (EPDs).
- Each rack holds 10 EPDs and racks can be stacked side by side to hold any number of dosimeters.
- Up to 5 racks supported by 2 wall brackets (2 brackets supplied per 5 wall racks)
- Racks lift off wall brackets and can be stowed directly in the EPD Transport Box for transfer to calibration laboratory, workshop or for emergency use.
- EPDs are secured with their displays facing outwards and the status of each EPD can be seen at a glance.



Transport Box TPB-1™

- Strong alloy box accepts wall racks complete with EPDs directly for quick and convenient transport around a site or off-site.
- Foam-lined lid holds EPDs securely, even if partially loaded.
- Holds up to 5 wall racks each with up to 10 EPDs
- Size: 680 x 530 x 130 mm (approx.), excl. handle
- Weight (with 50 EPDs) <16 kg (35 lbs)

Note: Order WR-1 Wall Racks separately



EPD MK2 Area Monitoring Case

- Real-time monitoring capabilities
- Light weight and portable
- Waterproof
- Customizable color case
- Various battery options: Rechargeable, D-cell up to 45 days of continuous operation
- DC power with battery back-up
- Solar power option for perimeter monitoring

External Alarm Unit

- LED light from the EPD activates the vibration and audio alarm through fiber hook
- Easily attached, optional, audible earpiece alarm
- Larger, brighter LED
- Vibrating alarm
- External audible alarm jack capability
- Alarm deactivation using reset button
- Rubber boot on fiber hook isolates other light sources
- Requires 9-volt battery
- Clip for easy attachment to clothing
- Rugged plastic case

EPD Spare Kits™

A range of spares kits are available for EPD Mk 2. Please contact Thermo Fisher Scientific for details



©2007 Thermo Fisher Scientific Inc. All rights reserved. Kapton is a registered trademark of E.I. du Pont de Nemours and Company. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Results may vary under different operating conditions. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. Literature Code LITEPDACCESSORIES 0407

Worldwide
Frauenauracher Strasse 96 +49 (0) 9131 909-0
D 91056 Erlangen, Germany +49 (0) 9131 909-205 fax

United Kingdom
Bath Road, Beenham, +44 (0) 118 971 2121
Reading RG7 5PR United Kingdom +44 (0) 118 971 2835 fax

United States
27 Forge Parkway +1 (508) 520-2815
Franklin, MA 02038 USA +1 (800) 274-4212 toll-free
+1 (508) 428-3535 fax

www.thermo.com/rmp

Thermo
SCIENTIFIC